

PIR Alarm Motion Sensor



PRODUCT CODE:

MED-NC-MS-02-T(X)

MED-NC-MS-02-T(X)(KIT) with power pack

(TGA Registration: 223902)

Indigo Care provides a 2-in-1 PIR Alarm Motion Sensor with wide and narrow beam. Also available is the Dual PIR Out-of-Bed Sensor with narrow beam for resident with risk of falling out-of bed.

The motion sensor should be placed upright in a position to monitor the resident's movements.

It can be wall mounted using the attached bracket. You can swivel the PIR to whatever direction you would like. This will enable you to obtain your desired beam position.

The motion sensor will be activated when the resident crosses the beam's path. The motion sensor is powered by a 9 Volt battery (not included) or by a 9 V DC Adaptor. There is a 3 meter cable (included) which connects to the motion sensor and your nurse call system. The plug is a 6.3mm jack contact us for wiring requirements.

The PIR can be activated manually using the ON/OFF switch.

KEY SPECIFICATIONS:

- Nurse Call and DC Output
- Included : Cable from PIR to Call Plate
- Horizontal Beam Angle
 - 6 deg (narrow beam)
 - Up to 80 deg (wide beam)
- Warranty: 12 months

REDUCE THE RISK OF
FALLS & POTENTIAL
INJURIES

STAND ALONE 2-IN-1
WITH WIDE AND
NARROW BEAM

NARROW BEAM CAN
BE USED AS OUT OF
BED ALARM

NARROW BEAM CAN
ALSO BE USED AS
OUT OF DOOR
ALARM

PORTABLE

EASY TO USE

INTEGRATE TO
MOST NURSE CALL
SYSTEMS

PLUG & PLAY
OPERATION



Horizon Electronic Components T/as INDIGO CARE
2/71 Rushdale Street, Knoxfield, VIC, 3180
PH +61 3 9763-2988 FAX +61 3 9763-3811
www.indigocare.com.au
ABN 36007302801

ORDER INFORMATION

Fax or email your purchase orders to
03-9763-3811
Or email sales@indigocare.com.au